

CP-Citopac GmbH	Fassung: 9	31.08.2026	Erstellt: T. Ladenberger	Freigegeben: A. Schiffbauer
-----------------	------------	------------	--------------------------	-----------------------------

Werkzeuge – Suppositorien-Modell „R“

Herstellungsmaße / manufacturing dimensions

Werkzeug-Nr.	Type	Füll- volumen ml	H	D	K	T	E	L
1/00 peel off	0,75	0,75	45 (51)	7,6	9,6	7,0	5,5	21,3
1/03 peel off	1.00	1,12	45 (51)	9,0	10,0	7,0	6,0	26,0
1/08 peel off	1,25	1,20	45 (51)	9,2	8,8	8,0	6,1	26,5
1/09 peel off	1,35	1,38	45 (51)	9,2	9,5	7,3	6,3	27,5
1/14 peel off	1,50	1,40	45 (51)	9,5	8,5	8,5	6,5	27,0
1/18 peel off	1,75	1,88	51	11,0	9,0	8,5	7,0	33,5
1/20	2,00	2.02	51	11,2	9,0	9,0	7,2	33,0
1/22 peel off	2,10	2,10	51	11,1	9,0	8,0	7,0	33,0
1/24 peel off	2,25	2,31	51	11,2	9,5	8,6	6,9	34,0
1/25 peel off	2,25	2,27	51	11,1	9,5	8,0	7,0	33,5
5/01 peel off	2,25	2,26	51	11,1	9,5	8,0	7,1	33,8
1/29 peel off	2,35	2,34	51	11,5	8,8	9,0	7,5	34,5
1/32 peel off	2,40	2,56	51	11,8	9,5	8,5	7,5	33,5
1/34 peel off	2,50	2,60	51	11,8	8,5	9,0	8,0	35,0
1/37 peel off	2,75	2,76	51	12,0	9,0	9,5	8,0	36,0
1/40	3,00	3,18	51	12,4	9,2	7,7	6,4	36,5
1/41 peel off	3,00	3,15	51	12,4	9,5	9,3	8,4	36,5

Toleranzen für H und K = 0,2 mm. Tolerances for H und K = 0,2 mm.

Die anderen Maße sind Werkzeuggebunden und können auf Grund der Folien
± 2% abweichen.

Other measures are bound to tools and can due to the film tolerance ± 2% differ.

